

故障现象：现场是冗余 I/O，但是模块报冗余报错，且报辅助电源丢失。

解决方案：

Hardware Rack Configuration:

Slot	Module	Order no.
0	IM155-6-PN-HA-V1.2	6DL1 132-6BH00-0PH1
X1	PN-IO	
X1 P1 R	Port 1 RJ45	6DL1 132-6BH00-0PH1
X1 P2 R	Port 2 RJ45	6DL1 132-6BH00-0PH1
7	IM155-6-PN-HA-Red	6DL1 132-6BH00-0PH1
X1	PN-IO-Red	
X1 P1 R	Port 1 RJ45	6DL1 132-6BH00-0PH1
X1 P2 R	Port 2 RJ45	6DL1 132-6BH00-0PH1
2	DI32 x 24V DC HA	6DL1 132-6BH00-0PH1
3	DI32 x 24V DC HA	6DL1 131-6BH00-0PH1
4	DI16 x 24VDC HA	6DL1 131-6BH00-0PH1
5	DI16 x 24VDC HA	6DL1 131-6BH00-0PH1
6	DQ16 x 24VDC/0.5A HA	6DL1 132-6BH00-0PH1
7	DQ16 x 24VDC/0.5A HA	6DL1 132-6BH00-0PH1
8	DQ16 x 24VDC/0.5A HA	6DL1 132-6BH00-0PH1
9	DQ16 x 24VDC/0.5A HA	6DL1 132-6BH00-0PH1
10	DQ16 x 24VDC/0.5A HA	6DL1 132-6BH00-0PH1
11	DQ16 x 24VDC/0.5A HA	6DL1 132-6BH00-0PH1
12	AQ8 x I HART HA	6DL1 132-6BH00-0PH1
12.0	HART Field Device	
12.1	HART Field Device	
12.2	HART Field Device	
12.3	HART Field Device	
12.4	HART Field Device	
12.5	HART Field Device	
12.6	HART Field Device	
12.7	HART Field Device	
13	AQ8 x I HART HA	6DL1 132-6BH00-0PH1
13.0	HART Field Device	
13.1	HART Field Device	
13.2	HART Field Device	
13.3	HART Field Device	
13.4	HART Field Device	
13.5	HART Field Device	
13.6	HART Field Device	
13.7	HART Field Device	
14	AQ8 x I HART HA	6DL1 132-6BH00-0PH1
14.0	HART Field Device	
14.1	HART Field Device	
14.2	HART Field Device	
14.3	HART Field Device	
14.4	HART Field Device	
14.5	HART Field Device	
14.6	HART Field Device	
14.7	HART Field Device	
15	AQ8 x I HART HA	6DL1 132-6BH00-0PH1

Diagnostic Window: 属性 - DI16 x 24VDC HA - (R-/S4)

参数

- Parameters
 - Diagnostics Missing supply voltage L+
 - Cross-channel
 - Channel 0
 - Channel 1
 - Channel 2
 - Channel 3
 - Channel 4
 - Channel 5
 - Channel 6
 - Channel 7
 - Channel 8
 - Channel 9
 - Channel 10
 - Channel 11
 - Channel 12
 - Channel 13
 - Channel 14
 - Channel 15
 - Double-width terminal block
 - Potential group
 - Potential group
 - Potential group of the left mo...

一对冗余I/O的右侧卡件
这里边没有供电。
改成从左侧来供电